

Item
2324


1. Product Description:

Disco Flap de Felpa

Dimensions (in):	4-1/2" x 7/8"
Dimensions (mm):	115 x 22.23
Specification:	FELPA D5/H25
RPM Óptimas:	1,650
Max. rpm:	8,500



27 LAM



D= 115 mm
H= 22.23 mm



1. Application

- For polishing with polishing compounds on materials such as metals, stainless steel, non-ferrous metals, plastic, and marble.
- Each wool flap helps reduce heat buildup and provides greater control over the surface finish.
- Ideal for achieving a mirror finish.
- Manufactured with premium-quality wool.



Angle
Grinder



Satin
Finishing
Sander

- Always wear appropriate personal protective equipment (PPE), including gloves, hearing protection, respiratory protection, and safety glasses.
- Improper use may result in serious injury.

4. Handling

- Initial inspection should be performed while the product is in its original packaging. If there is visible evidence of damage, the product should not be accepted.
- Handle the discs carefully to prevent tearing or breakage. If a disc is torn, has a detached section, or is suspected of being damaged, it must not be mounted or used.

5. Storage

- Store the discs flat, at least 10 cm (4 in) above floor level, away from damp, cold, or hot surfaces and from any type of fluid. Ideal storage conditions are 40–50% relative humidity and a temperature between 15 and 29 °C (59–84 °F).

6. Packaging units

- 5 pieces.

2. Operating instructions

- For use with an angle grinder or variable-speed satin finishing machine.
- Use with polishing compounds, applying them at low operating speeds.
- Mount the disc and allow it to run at no-load speed for one minute to verify that it is not damaged.
- Maintain the disc at an angle of 0° to 15° to the workpiece surface for best results.
- Do not apply excessive pressure or strike the disc against the workpiece.
- The optimal operating speed for polishing is between 1,650 and 2,500 rpm.

3. Safety information

- Never exceed the maximum operating speed indicated on the product label.